



CERTOTTICA

Istituto Italiano per la Certificazione dei Prodotti Ottici Scarl
Loc. Villanova Zona Industriale - 32013 LONGARONE BL
Tel.: +39 0437 573157 - TeleFAX: +39 0437 573131
Web: www.certottica.it **E-mail:** info@certottica.it

Page 1 / 11
Rep. No. 110093

Organismo Notificato UE n. 0530 - Autorizzato dal Ministero dello Sviluppo Economico e dal Ministero del Lavoro e della Previdenza Sociale con D.L. 12/12/07.

TEST REPORT

Client:	BOLLE' PROTECTION
Address:	95 rue Louis Guérin - 69 100 VILLEURBANNE FRANCE
Article:	Spectacle
Model:	ASSAULT ESP lens
Job no.:	C110032
Report no.:	110093
Receiving Date:	22/12/2010
Date of Test Begin:	22/01/2010
Date of Test End:	15/02/2011
Issuing Date:	15/02/2011
Standard Applied:	EN 166:2001 - Personal eye-protection - Specifications

Note 1: This Test Report is valid exclusively for the specimens utilized for tests and any modification shall be solely performed with the issuing of a new test report.

Note 2: The partial reproduction of this Test Report is permitted against written authorization by Certottica.

Note 3: The Test Report in digital format and the relevant attached file of the digital signatures are official documents. The validity of this Test Report can be checked at <http://www.certottica.org>.

Note 4: The tests were performed on specimens that sampled the customer.

Optical Tests

Quality of material and surface

Clause 7.1.3

Requirements

Except for a marginal area 5 mm wide, oculars shall be free from any significant defects likely to impair vision in use.

Outcomes

Sample	Defects	Test
110093 4dx	—	Pass
110093 4sx	—	Pass
110093 5dx	—	Pass
110093 5sx	—	Pass
110093 6dx	—	Pass
110093 6sx	—	Pass

Diffusion of light

Clause 7.1.2.3

Requirements

The measurement of the reduced luminance factor is performed following the method stated in the EN167 Clause 4.2.1 (basic method). The reduced luminance factor shall be not superior than $1 \text{ cd m}^{-2} \text{ lx}^{-1}$ for welding filters, $0.75 \text{ cd m}^{-2} \text{ lx}^{-1}$ for oculars used in eye-protectors against high speed particles, $0.5 \text{ cd m}^{-2} \text{ lx}^{-1}$ for all other oculars.

Outcomes

Sample	l^* ($\text{cd m}^{-2} \text{ lx}^{-1}$)	Test
110093 4dx	0.09	Pass
110093 4sx	0.04	Pass
110093 5dx	0.10	Pass
110093 5sx	0.12	Pass
110093 6dx	0.07	Pass
110093 6sx	0.10	Pass

Transmittance

Clause 7.1.2.2

Oculars with filtering action (filters) and housings for oculars with filtering action

Clauses 7.1.2.2.2, 7.2.1

Requirements

The transmittance requirements for filtering oculars are specified in the EN 169 - *Welding filters*, EN 170 - *Ultraviolet filters*, EN 171 - *Infrared filters*, EN 172 - *Sunglare filters for industrial use* and EN 379, *Welding filters with switchable luminous transmittance*.

Goggles and face-shields mounting filtering oculars shall provide at least the same level of protection as given by the oculars.

Permissible transmittance and scale numbers

EN172 - Clause 4

Measurement Method of the Spectral Transmittance

The spectral transmittance is measured at least from 280 to 780 nm and at no more than from 280 to 2000 nm, always with the step of 1 nm through a spectrophotometer using a spectral band width not superior to 2 nm in the ultraviolet and in the visible and not over 20 nm in the infrared.

Sample Labeling and Measurement Point

The sample labeling and the measurement points are explained as following.

The measurement point on a filter is the standard's reference point if not otherwise specified. The reference point is the visual point or the geometric point if the first is unknown.

The spectral transmittance measurement points are labeled by mean a serie of strings.

The strings s_x e d_x identified the left and the right oculars reference point respectively.

The mounted gradient filters generally are measured in the reference point and in the points at the most 15 mm up and below the reference point and along the two parallels to the line through the right and the left reference points of the protective equipment.

In the case of unmounted singular filter the measurement are performed along the gradient direction.

The two measurement points apart the reference point are labeled s and c .

Photochromic filters can to be measured at different conditions of temperature, T (unit Celsius degree), and illumination, L (unit lux), and the labeling is performed with a suffix.

Luminous Transmittance

EN172 - Clause 4.1

Requirements

The superior and inferior limits of T_v relative to a filter shade number are showed in the Tables 1 and 2 of the standard.

Outcomes

The measurement values of T_v , expressed in percent, and the relative test are:

Sample	T_v (%)	Test
110093 4sx	60.0	Pass
110093 4dx	61.1	Pass
110093 5sx	59.7	Pass
110093 5dx	68.2	Pass
110093 6sx	58.9	Pass
110093 6dx	61.3	Pass

Ultraviolet and Visible Spectral Transmittance

EN172 - Clause 4.1

Requirements

The superior values of the spectral transmittance, $T(\lambda)$, from 280 to 315 nm, here named T_{max280_315} , and of the transmittance, $T(\lambda)$, from 315 to 350 nm, here named T_{max315_350} , must be conform to the requirements in the Tab. 1 and 2 of the standard.

The mean value of $T(\lambda)$ from 315 to 380 nm, here named $T_{mean315_380}$, must be conform to the requirements in the Tab. 1 and 2 of the standard.

The minimum value of $T(\lambda)$ from 500 to 650 nm, here named T_{min500_600} , must be not inferior to 1/5 of the T_v .

Outcomes

Measurement values and the result of the tests are:

Sample	Tmax280_315 (Tv)	Test	Tmax315_350 (Tv)	Test	Tmean315_380 (Tv)	Test
110093 4sx	0.00	Pass	0.00	Pass	0.00	Pass
110093 4dx	0.00	Pass	0.00	Pass	0.00	Pass
110093 5sx	0.00	Pass	0.00	Pass	0.00	Pass
110093 5dx	0.00	Pass	0.00	Pass	0.00	Pass
110093 6sx	0.00	Pass	0.00	Pass	0.00	Pass
110093 6dx	0.00	Pass	0.00	Pass	0.00	Pass

Recognition of signal lights

EN172 - Clause 4.2

Requirements

Nota: these specifications are applicable to filters with shade number from 1 to 3,1.

The Q-factor of the semaphoric signals red, yellow, green and blue, here named respectively Qred, Qyellow, Qgreen e Qblue, must be not inferior to 4/5.

Outcomes

The measurements values of Qred, Qyellow, Qgreen e Qblue and the results of the tests are:

Sample	Qred	Test	Qyellow	Test	Qgreen	Test	Qblue	Test
110093 4sx	1.11	Pass	1.06	Pass	0.97	Pass	0.94	Pass
110093 4dx	1.11	Pass	1.06	Pass	0.96	Pass	0.94	Pass
110093 5sx	1.10	Pass	1.06	Pass	0.97	Pass	0.94	Pass
110093 5dx	1.07	Pass	1.04	Pass	0.98	Pass	0.96	Pass
110093 6sx	1.10	Pass	1.06	Pass	0.97	Pass	0.94	Pass
110093 6dx	1.10	Pass	1.06	Pass	0.97	Pass	0.94	Pass

Spectral transmittance

EN172 - Clause 4.2

Requirements

Note: these specifications are applicable to filters with shade number from 1 to 3,1.

The minimum value of the spectral transmission factor in the wavelength interval from 500 to 650 nm, here named Tmin500_650, shall not be inferior to 0.2 Tv for filters declared appropriate for driving and use on the road.

Outcomes

The minimum value measured of the spectral transmittance from 500 to 650 nm, is:

Sample	Tmin500_650 (Tv)	Test
110093 4sx	0.88	Pass
110093 4dx	0.88	Pass
110093 5sx	0.89	Pass
110093 5dx	0.91	Pass
110093 6sx	0.88	Pass
110093 6dx	0.88	Pass

On road use: day Yes ; night NO .

Scale Number

EN166 Clause 5

Requirements

The scale numbers are defined by Table 1 of the EN166.

Outcomes

The filter scale number determined is:

Sample	Scale Number
110093 4sx	5 - 1,4
110093 4dx	5 - 1,4
110093 5sx	5 - 1,4
110093 5dx	5 - 1,4
110093 6sx	5 - 1,4
110093 6dx	5 - 1,4

Variations in transmittance (Oculars without filtering action are exempt from this requirement)

Clause 7.1.2.2.3

Oculars without corrective effect

Clause 7.1.2.2.3.1

Requirements

The relative variation of the luminous transmittance around the visual centre(s) P_1 (and P_2) shall not exceed the values stated in Table 4 of the standard.

The relative difference in luminous transmittance, P_3 , between left and right oculars shall not exceed the values stated in Table 4 of the standard or 20% whichever is greater.

Outcomes

Sample	P_1 (%)	Test	P_2 (%)	Test	P_3 (%)	Test
110093 4	2	Pass	1	Pass	2	Pass
110093 5	1	Pass	2	Pass	12	Pass
110093 6	1	Pass	1	Pass	4	Pass

Resistance to ultraviolet radiation (oculars only)

Clause 7.1.5.2

Requirements

The external surface of the filters is exposed to radiation of a 450W Xenon lamp. The exposure time is 50 hours, the distance between filter and lamp is 300 mm, and the test equipment operate at environment temperature of 23 ± 5 Celsius degrees.

The absolute value of the relative variation of T_v after radiation shall not be greater than the values specified in Table 6 of EN166.

Measurement value of ℓ^* after radiation shall be not higher than 1, 0.75, $0.5 \text{ cd m}^{-2} \text{ lx}^{-1}$ respectively for welding filters, ocular for protection against high-speed particles, for all other type of oculars.

Outcomes

Measurement values of T_v and ℓ^* after irradiation, the relative variation of T_v and the test results are:

Sample	T_v (%)	$\Delta T_v/T_v$ (%)	Test	ℓ^* ($\text{cd m}^{-2} \text{ lx}^{-1}$)	Test
110093 4sx	59.3	-1	Pass	0.34	Pass
110093 4dx	59.9	-2	Pass	0.08	Pass
110093 5sx	59.7	0	Pass	0.20	Pass
110093 5dx	66.0	-3	Pass	0.17	Pass
110093 6sx	58.9	0	Pass	0.47	Pass
110093 6dx	60.2	-2	Pass	0.19	Pass

Spherical, astigmatic and prismatic powers

Clause 7.1.2.1

Note: The refractive powers of cover plates (see Clause 7.1.2.1.3 of the standard) shall comply with the tolerances for optical class 1 given in Tables 2 and 3 of the standard. The test results in the case of the cover plates here reported are relative to the optical class 1 requirements.

Mounted oculars and unmounted oculars covering both eyes

Clause 7.1.2.1.2

Requirements

Note: The refractive powers of cover plates shall comply with the tolerances for optical class 1 given in Tables 2 and 3 of the standard.

Outcomes

Sample	Sph. Refr. Pow. (D)	Test	Ast. Refr. Pow. (D)	Test
110093 101dx	-0.01	Pass	0.01	Pass
110093 101sx	0.00	Pass	0.02	Pass
110093 102dx	-0.01	Pass	0.01	Pass
110093 102sx	0.00	Pass	0.00	Pass
110093 103dx	-0.02	Pass	0.01	Pass
110093 103sx	0.00	Pass	0.00	Pass

Requirements

Note: The refractive powers of cover plates shall comply with the tolerances for optical class 1 given in Tables 2 and 3 of the standard.

Outcomes

Measurement values of the differences of the horizontal and vertical refractive prismatic powers, the base, the relative tests and the possible optical class, are:

Sample	Base	Horiz. Pris. Diff. (cm/m)	Test	Ver. Pris. Diff. (cm/m)	Test	Optical Class
110093 101	out	0.20	Pass	0.05	Pass	One
110093 102	out	0.30	Pass	0.10	Pass	One
110093 103	out	0.35	Pass	0.05	Pass	One

Stability at an elevated temperature*Clause 7.1.5.1***Requirements**

The protective equipment conditioned at the temperature of 55 ± 5 Celsius degrees for 60 ± 5 minutes, after 60 minutes at the environment temperature shall show no apparent deformation.

Outcomes

The test has given the following results:

Sample	Deformations	Test
110093 101	—	Pass
110093 102	—	Pass
110093 103	—	Pass

Mechanical Tests

General construction

Clause 6.1

Requirements

Eye-protectors shall meet the general construction requirements consisting in being free from projections, sharp edges or other defects which can cause discomfort or injury during normal use.

Outcomes

Specimen	Observations	Test
110093 1	—	Pass
110093 2	—	Pass
110093 3	—	Pass

Field of vision

Clause 7.1.1

Requirements

Eye-protector shall have a field of vision including for each eye the field defined by a cone having its vertex in the pupil and such to form an ellipse with its section on a 25mm distant plane parallel to the two pupils and orthogonal to the horizontal sight axis. The ellipses have the following geometric features: horizontal axis 22 mm, vertical axis 20 mm. The horizontal axis shall be parallel to and 0.7 mm below the height of the line connecting the centres of the two eyes; the horizontal displacement of the ellipse's centre is 3 mm toward the external eye side.

Outcomes

The performed tests have given the following results:

Specimen	Observations	Test
110093 1	—	Pass
110093 2	—	Pass
110093 3	—	Pass

Robustness

Clause 7.1.4

Increased robustness

Clause 7.1.4.2

Complete eye-protectors and frames

Clause 7.1.4.2.2

Requirements

The eye protector shall be submitted to an impact of a 22 mm diameter steel ball, of 43 g minimum mass at a speed of 5.1 m/s. The impact occurs in correspondance to the visual centers and the eye-sides.

As a consequence of the test, the sample shall not present any ocular fractures or deformations, ocular housing fractures, frame fractures, lateral protection failure.

Before the test, samples are pre-conditioned for at least one hour at -5 or +55 Celsius degrees.

The possible impact points are the ocular centres and the lateral protection.

A new sample shall be used for each impact point.

Outcomes

The results of the test are:

Sample	Impact Point	Temperature (° C)	Observations	Test
110093 7	right frontal	+55	—	Pass
110093 8	left frontal	+55	—	Pass
110093 9	right side	+55	—	Pass
110093 10	left side	+55	—	Pass
110093 11	right frontal	+55	—	Pass
110093 12	left side	+55	—	Pass
110093 13	right frontal	-5	—	Pass
110093 14	left frontal	-5	—	Pass
110093 15	right side	-5	—	Pass
110093 16	left side	-5	—	Pass
110093 17	left frontal	-5	—	Pass
110093 18	right side	-5	—	Pass

Resistance to ignition*Clause 7.1.7***Requirements**

The several external parts of the test sample except elastic headbands and textile edging, are put into direct contact for 5 ± 0.5 seconds with a steel bar risen to the temperature of 650 ± 20 Celsius degrees. During the test, a visual exam is performed to establish if the test sample ignite or continue to glow after the removal of the steel bar.

Outcomes

The visual exam has given the following results:

Sample	Observations	Test
110093 10	—	Pass
110093 11	—	Pass
110093 12	—	Pass

Lateral protection*Clause 7.2.8*

Requirements

The eye-protector shall give lateral protection of the ocular region. The test consists to verify that the lateral and the frontal impact point of the headform are protected by the device to test, into an area of radius 10 mm.

Outcomes

The results of the test are:

Sample	Observations	Test
110093 1	—	Pass
110093 2	—	Pass
110093 3	—	Pass

Protection against high Speed particles at extremes of temperature*Clause 7.3.4***Requirements**

If an increased impact resistance is required, the complete eye-protector shall withstand the impact of a 6 mm nominal diameter steel ball of 0.86 g minimum mass striking the ocular at one of the speeds 45, 120 or 190 m/s according to the robustness declared.

The impact are carried out after the protector have been conditioned at $+55 \pm 2$ and -5 ± 2 Celsius degrees, in correspondence to the visual centre and of the lateral protection.

Outcomes

The performed tests have given the following results:

Sample	Impact point	Temperature (° C)	Speed (m/s)	Defects	Test
110093 45	right frontal	+55	45.2	—	Pass
110093 46	left frontal	+55	46.0	—	Pass
110093 47	right side	+55	45.8	—	Pass
110093 48	left side	+55	46.1	—	Pass
110093 49	right frontal	+55	46.3	—	Pass
110093 50	left side	+55	45.4	—	Pass
110093 51	right frontal	-5	45.4	—	Pass
110093 52	left frontal	-5	45.6	—	Pass
110093 53	right side	-5	45.7	—	Pass
110093 54	left side	-5	45.9	—	Pass
110093 55	left frontal	-5	46.2	—	Pass
110093 56	right side	-5	46.0	—	Pass

Optical laboratory manager: Renato Battistin

Protective laboratory manager: Michele Molinari

Laboratory Technical Manager: Giorgio Sommariva



Figure 1: Specimen picture.